



MM6 ENHANCED CHANNEL RACK, 6.5" D CHANNEL, 7' H, 45 RU, TAPPED #12-24

MM6E706 | [Ortronics](#)

FEATURES & BENEFITS

The Mighty Mo 6 Enhanced Racks have been designed to update any building network and provide the optimal flexibility in cable management. The new cable hive sidewall design increases usability of the channel sidewalls for cable bundle tie locations. Mighty Mo 6 Enhanced is available in 6', 7' and 8' versions in all depths of 6.50", 10.50", and 16.25". When used with the Q-Series Vertical Manager, the Mighty Mo 6E becomes the very best in versatility and value.



Percent Energy Savings:

- **3 PC waterfall design:** Can install after rack assembly
- **Bonding and grounding per UL 2416:** Each channel rack has a unique bonding feature that requires no additional hardware or installation
- **Cable hive sidewalls:** The Mighty Mo 6 Enhanced Channel Sidewalls contain multiple "cable hive" locations which allow for many cable bundles to be safely tied to the sidewalls
- **UL Static load rating:** All versions of the Mighty Mo 6 Enhanced Channel Racks are UL rated for 1500 lbs. static load
- **Vertical management options:** Channel racks can be installed with the standard Mighty Mo 6 Manager or the Q-Series Lightweight Vertical Manager
- **Support angle feet:** Each rack is equipped with support angle feet in the front and rear, which allows for bolting to the floor
- **Open rack top:** The top of the Mighty Mo 6 Enhanced Rack is open for additional cable egress
- UL file number E349535
- Center opening for additional cable drops
- Lightweight plastic

SPECIFICATIONS

GENERAL INFO

Available Internationally: Yes

Color: Black

Product Series: Mighty Mo 6 E

Type: Cable Management Racks

Component Type: Channel Rack

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CONSTRUCTION INFORMATION

Component 2:

Material 1: Aluminum

Material 2: PC ABS

DIMENSIONS

Depth (Metric): 165.10mm

Depth (US): 6.50in

Height (Metric): 2184.40mm

Height (US): 86in

Width (Metric): 603.25mm

Width (US): 23.75in

Rack Units: 45

TECHNICAL INFORMATION

Static Load Capacity: 1500 lbs

Equipment Type: Open Racks

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

