



## SWING-EZ WALL RACK, HEAVY DUTY, GRAY, 25.00"D

OR-19-21-T25DHYDT | [Ortronics](#)

### FEATURES & BENEFITS

19.75"W x 24.25"H x 25.00"D



- Swing-EZ Wall Racks offer flexibility:**The 25" deep unit gives the flexibility of mounting equipment where space is a premium and a full size rack cannot be used for small offices.
- Front swing gate with latch pins and bolts on both sides:**Allows you to open swing gate either left or right and easy access to rear of panels and equipment.
- #12-24 threaded EIA hole pattern:**Standards compliant to mount numerous types of 19" panels and equipment.
- Side panels fold flat for shipping:**Unfold for easy on site assembly.
- Reinforcement pan attached to bottom of Swing-EZ :**Sturdy and holds equipment up to 150lbs.
- Compact:**11 rack units (1.75").
- Base includes 3" feed through holes:**Allows cable delivery from bottom of rack.
- Self squaring assembly:**No additional tools required.
- One-Wrap brand Velcro straps included:**hook and loop slots located on the rear for cable management.
- Includes 12-24 mounting screws :**Do not have to purchase as separate item.

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray  
Product Series: Swing-EZ  
Type: Wall Mount Racks

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Depth (Metric): 637 mm  
Depth (US): 25.00"  
Height (Metric): 616 mm

Height (US): 24.25"  
Width (Metric): 508 mm  
Width (US): 19.75"  
Rack Units: 11