



SWING-EZ WALL RACK, GRAY, 8.00"D

OR-19-21-T8D | [Ortronics](#)

FEATURES & BENEFITS

19.75"W x 21.00"H x 8.00"D



PRODUCT
ENVIRONMENTAL PROFILE

- Swing-EZ Wall Racks offer flexibility:**The 8" deep unit gives the flexibility of mounting equipment where space is a premium and a full size rack cannot be used for small offices.
- Front swing gate with latch pins and bolts on both sides:**Allows you to open swing gate either left or right and easy access to rear of panels and equipment.
- #12-24 threaded EIA hole pattern:**Standards compliant to mount numerous types of 19" panels and equipment.
- Side panels fold flat for shipping:**Unfold for easy on site assembly.
- Sturdy and compact:**Holds equipment up to 75 lbs with the use of 11 rack units (1.75").
- One-Wrap brand Velcro straps included:**Velcro slots located on the rear for cable management.
- Includes 12-24 mounting screws :**Do not have to purchase as separate item.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Product Series: Swing-EZ
Type: Wall Mount Racks

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Depth (Metric): 203 mm
Depth (US): 8.00"
Height (Metric): 538 mm
Height (US): 21.00"
Width (Metric): 510 mm
Width (US): 19.75"

Rack Units: 11