
FIXED DUAL SHELF, VENTED, 1.56"H X 17.50" W X 32.50"D

OR-ESV-19-SDR2732F | [Ortronics](#)



FEATURES & BENEFITS

Dual Fixed Shelf, Vented, 1.56"H x 17.50" W x 32.50"D, center load rating: 125 lbs., distributed load rating: 300 lbs.



- Mounts to all Ortronics adjustable dual equipment racks
- Heavy-duty for high load bearing capacity
- Bottom brackets adjust to rack depth
- Easy to add and remove deep equipment
- Fully usable surface area to accommodate servers
- Air flow slots ensure equipment is kept cool
- 12-24 cage nuts and screws included
- Steel construction with black finish

SPECIFICATIONS

GENERAL INFO

Type: Shelves
Features: Vented

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CONSTRUCTION INFORMATION

Component 1: Shelf
Finish Plating 1: Powder coat black
Material 1: 16 GA (.0598) CRS

DIMENSIONS

Capacity Weight (US): center load rating: 125 lbs, distributed load rating: 300 lbs
Depth (Metric): 826 mm
Depth (US): 32.50"
Height (Metric): 40 mm
Height (US): 1.56"
Width (Metric): 445 mm
Width (US): 17.50"
Product Weight (US): 18.0 lbs
Rack Units: 1

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

