

25FT RAPIDRUN®; MULTI-FORMAT RUNNER CABLE - CMG-RATED

60003 | [Quiktron](#)

FEATURES & BENEFITS

RapidRun® is designed to be the standard for in-wall audio/video installations. Using pre-terminated Break-away flying leads and wall plates with an in-wall runner ensures flexible, efficient, high quality connections for all types of equipment, with no field terminations.

Electrical Characteristics

3 Coax Conductor:

- Impedance: $75\pm 5\Omega$
- Capacitance: $71\pm 2\text{pF/ft}$
- Velocity of propagation: $78\pm 1\%$
- DC resistance: $237\pm 10\Omega/\text{km}$
- Dielectric strength: 500VAC/1 minute min.
- Insulation resistance (500V): $10\text{M}\Omega/\text{KM}$

3 Twisted Pair Conductors

- DC resistance: $93.25\Omega/\text{m}$ at 20°C
- Dielectric strength: 750VAC/minute min.
- Insulation resistance: $100\text{M}\Omega/\text{KM}$ at 20°C

Physical Characteristics

- Voltage rating: 30V
- Temperature rating: 80°C
- Temperature range: $-25^\circ - 80^\circ\text{C}$
- Minimum bend radius: 90mm

Conductor (qty. 3)

- Conductor type: 28AWG (7/0.127) (tinned copper)
- Dielectric: Foam PE
- Shield: Spiral shield (tinned copper) (90% coverage)
- Insulation: PVC

Conductor (qty. 3 twisted pair)

- Conductor type: 24AWG (7/0.2) (tinned copper)
- Foil shield: Aluminum foil (100% coverage)
- Insulation: PVC

Conductor (qty. 2 conductors)

- Conductor type: 24AWG (7/0.2) (tinned copper)
- Insulation: PVC

Overall Cable

- Foil shield: Aluminum foil (100% coverage)
- Braided shield: 24/8/0.12 (tinned copper) (85% coverage)
- Jacket: Matte PVC - CMG rated

RapidRun Din Connector

- Connector type: 15-pin DIN
- Contact material: Brass, $3\mu\text{m}$ gold plating
- Insulation: Black PBT
- Dimensions (DxL): 16.0 x 39.0mm

SPECIFICATIONS

GENERAL INFO

Color: Black

Product Series: RapidRun

Type: RapidRun Multi-Format Runners