
BLANK PLATE -- BOX MOUNTED, TWO GANG, 430 STAINLESS STEEL

SL23 | [Pass & Seymour](#)



FEATURES & BENEFITS

Smooth Metal Wall Plate, 2gang Blank, Box Mounted, 430 Stainless Steel



- Type 430 Stainless Steel, magnetic: .032" nominal thickness.
- Brushed finish.
- Less corrosion-resistant than Type 302, but ideal for general service in high abuse applications in industrial plants, commercial, and industrial buildings.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

SPECIFICATIONS

GENERAL INFO

Size: Standard
Type: Box Mount
Style: Blank Plate

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CUL Listing No: No
cULus: No

cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121704
UR: No

TECHNICAL INFORMATION

Material: 430 Stainless Steel
Capacity: 2-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

