



1200 SERIES CABLE REEL WITH 20A QUAD
RECEPTICAL BOX
 20 AMP, 12 AWG,
50 FEET
 FOR LIFT/DRAW
APPLICATIONS </BR></BR>

CR12L123N50R20 | [Pass & Seymour](#)

FEATURES & BENEFITS

Industrial-grade 1200 Series Cable Reels are precision machines, built with a minimum of components to provide years of reliable service with little or no maintenance. Made of all steel construction in the USA, these cable reels are ideal for assembly and fabrication work areas, conveyors, utility trucks, automotive and truck work bays, and much more.

- Made in USA
- All steel construction with fiberglass/nylon drum, yellow powder coat finish
- UL/CSA Listed

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Product Series: 1200 Series

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listed: Yes

DIMENSIONS

Overall Dimensions (US): See Product Drawing for Dimensions

CORD INFORMATION

Cord Length US: 50 ft

TECHNICAL INFORMATION

Amps: 20

Operating Temperature (Celsius): -30° to 90°

Wire Gauge: 12 AWG 3C

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status:

