



1400 SERIES CABLE REEL WITH FLYING
LEAD
 25 AMP, 10 AWG, 60 FEET

 FOR LIFT/DRAG APPLICATIONS
</BR></BR>

CR14L103N60F25 | [Pass & Seymour](#)

FEATURES & BENEFITS

The 1400 Series Industrial Cable Reels are the professionals' choice for demanding industrial applications where reliability and versatility are paramount. Made in the USA with a minimum of components, these reels are ideal for assembly and fabrication work areas, Class A/C overhead cranes and hoists, schools and theaters, and much more.



- Made in USA
- Steel frame construction, black thermoplastic slip ring cover, yellow powder-coat finish
- NEMA 4 rated enclosure
- UL and CSA Listed

SPECIFICATIONS

GENERAL INFO

Color: Yellow
Product Series: 1400 Series

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listed: Yes

DIMENSIONS

Overall Dimensions (US): See Product Drawing for Dimensions

CORD INFORMATION

Cord Length US: 60 ft

TECHNICAL INFORMATION

Amps: 25

Operating Temperature (Celsius): -30° to 90°

Wire Gauge: 10 AWG 3C

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status:

