



1400 SERIES CABLE REEL WITH FLYING  
LEAD <BR> 16 AMP, 12 AWG, 30 FEET  
<BR> FOR STRETCH APPLICATIONS </BR>  
</BR>

CR14S124N30F16 | [Pass & Seymour](#)

---

## FEATURES & BENEFITS

The 1400 Series Industrial Cable Reels are the professionals' choice for demanding industrial applications where reliability and versatility are paramount. Made in the USA with a minimum of components, these reels are ideal for assembly and fabrication work areas, Class A/C overhead cranes and hoists, schools and theaters, and much more.

- Made in USA
- Steel frame construction, black thermoplastic slip ring cover, yellow powder-coat finish
- NEMA 4 rated enclosure
- UL and CSA Listed

---

## SPECIFICATIONS

### GENERAL INFO

Color: Yellow

Product Series: 1400 Series

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listed: Yes

### DIMENSIONS

Overall Dimensions (US): See Product Drawing for Dimensions

### CORD INFORMATION

Cord Length US: 30 ft

### TECHNICAL INFORMATION

Amps: 16

Operating Temperature (Celsius): -30° to 90°

Wire Gauge: 12 AWG 4C

### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status:

