



TRADEMASTER DECORATOR RECEPTACLES

TM8851150 | [Pass & Seymour](#)

FEATURES & BENEFITS

Decorator duplex receptacle with pressure plate. 15 amp, 125 volt, Ivory. 150 pack.



PRODUCT
ENVIRONMENTAL PROFILE

- Longer steel straps than competitive devices, still fits under a standard wall plate.
- High-impact thermoplastic face and back body eliminate cracks, breaks, and callbacks.
- Ultrasonic welding of face to back body.
- Patented design provides better plug retention.
- External screw-pressure-plate back wire on all four terminal screws and ground screw eliminates wrapping.
- Accepts #12 and #14 stranded and solid wire.
- Break-off tabs that are big enough to grab hold of -- even if contact screws are backed out.
- Scored deeper for fast, clean breaks every time.
- All four contact screws and the ground screw are backed out.
- All screws are tri-drive.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Number Of Poles: 2
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121704

DIMENSIONS

Depth (US): 1"

Height (US): 3.31"

Width (US): 1.29"

TECHNICAL INFORMATION

Amps: 15A

Volts: 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

