



LS TRADEMASTER®; CFL/LED/INCANDESCENT SINGLE-POLE, NON-PRESET DIMMER, WHITE

LSCL450W | [Pass & Seymour](#)

FEATURES & BENEFITS

Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.



- CFL/LED dimmable bulb compatible (except for 0-10V LED drivers).
- Works with dimmable CFL/LED or Incandescent lighting loads at 450W CFL/LED & 700W Incandescent
- Built-in electromagnetic and radio-frequency interference protection.
- No dirt-catching crevices.
- Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plates available for all models.
- Preset ON/OFF switch automatically returns controlled lights to preset level without re-adjusting dimmer setting.
- Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.
- Superior heat management.
- Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.
- Rating: 450W LED & CFL; 700W Incandescent; 120VAC 60Hz.

SPECIFICATIONS

GENERAL INFO

Color: White
Product Series: LS TradeMaster
Type: CFL/LED
Number Of Poles: 1

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

DIMENSIONS

Depth (US): 1.28"

Height (US): 4.19"

Width (US): 1.74"

TECHNICAL INFORMATION

Volts (AC): 120

Watts: 450