



TRADEMASTER CFL/LED/INCANDESCENT SINGLE POLE/3-WAY TOGGLE DIMMER, LIGHT ALMOND

TDCL453PLA | [Pass & Seymour](#)

FEATURES & BENEFITS

Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control. The TDCL453P is convenient to operate with a standard ON/OFF toggle switch and separate dimming wheel for precise dimming control. Use specific suffix for color: W- white, BK- black, LA- light almond, I- ivory and no suffix for brown.



- Tough, impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.
- Preset, Single Pole/3-Way
- For covering patents, see www.legrand.us/patents.
- Rating: 450W LED & CFL; 700W Incandescent; 120VAC 60Hz.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Available Colors: White, Ivory, Light Almond, Black, and Brown
Product Series: TradeMaster
Type: CFL/LED Toggle
Number Of Poles: 1 , 3-way
Style: Toggle

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No. 184

CSA Standard: Yes
cULus: Yes
UL Standard: Yes

DIMENSIONS

Depth (US): 1.25"
Length (US): 4.25"
Width (US): 1.75"

TECHNICAL INFORMATION

Volts: 120V
Volts (AC): 120 VAC, 60Hz
Watts: 450W CFL or LED / 700W Incandescent

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No