



## TOGGLE SLIDE DIMMER CFL/LED, SINGLE POLE / 3-WAY 300W, RED

TSDCL303PRED | [Pass & Seymour](#)

### FEATURES & BENEFITS

Replace your standard switch with the new Toggle Slide Dimmer by Legrand. The new Toggle Slide Dimmer offering has been optimized for today's complicated dimmable bulb market. Different bulbs require different dimming solutions and Legrand has you covered for all your lighting needs. The ergonomic slider was designed with the end user in mind making it easier to adjust in the dark or on the run.

- New aesthetically pleasing ergonomic design allows for easier operation.
- Convenient operation—combines ON/OFF toggle switch with separate slider for dimming control.
- All models are capable of single pole and 3-way operation.
- Rating: 300W CFL / LED; 700W Incandescent; 120VAC, 60Hz
- Constant memory returns lights to previous levels after a power failure.
- Screw-pressure-plate backwire terminals save time, space and money.
- Seven additional face cover colors available but sold separately (see TSDKIT\*).
- Lifetime Warranty

### SPECIFICATIONS

#### GENERAL INFO

Secure Environment: Indoor Use Only  
Color: Red  
Type: CFL/LED Toggle  
Number Of Poles: Single Pole / 3-Way  
Number Of Wires: None  
Style: Toggle

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listed: Yes  
cULus: Yes  
UL Standard: UL1472

#### DIMENSIONS

Depth (US): 1.40"  
Height (US): 4.19" ( 2.68")

Length (US): 4.19" ( 2.68")  
Width (US): 1.73"  
Product Weight (US): 3.53 oz.

#### **TECHNICAL INFORMATION**

Material: Polycarbonate  
Volts: 120V  
Volts (AC): 120 VAC  
Watts: 300W CFL / LED; 700W Incandescent  
Grade Type: Spec Grade

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA  
Buy American Act Status: No