



WIDE SLIDE TRADEMASTER®; SINGLE-POLE, NON-PRESET CFL/LED SLIDE DIMMER, 3 INTERCHANGEABLE FACE PLATES

WSCL450TC | [Pass & Seymour](#)

FEATURES & BENEFITS

Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.



- Convenient Operation - Combines ON/OFF Decorator-style switch with separate slider for dimming control.
- Constant memory returns lights to previous level after a power failure.
- Sleek, ergonomic design that matches well with other decorator products.
- Higher ratings.
- Single-pole operation.
- Screw-pressure-plate back wire terminals save time, space and money.
- Rating: 450W LED & CFL; 700W Incandescent; 120VAC 60Hz.

SPECIFICATIONS

GENERAL INFO

Color: Tri-Color (Ivory, White, Light Almond)
Product Series: Wide Slide TradeMaster
Type: CFL/LED
Number Of Poles: 1

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes

DIMENSIONS

Depth (US): 1.25"
Height (US): 4.25"
Width (US): 1.75"

TECHNICAL INFORMATION

Volts (AC): 120

Watts: 450