



## LS SERIES INCANDESCENT SLIDE DIMMER, BLACK

LS603PBK | [Pass & Seymour](#)

### FEATURES & BENEFITS

Incandescent Slide Dimmer, Preset 3way 600W, Black



- Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.
- Electromagnetic and radio-frequency interference protection built in.
- Sleek, sculpted contemporary design. No dirt-catching crevices.
- Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.
- Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.
- Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.
- Superior heat management.
- No derating on 600W units.
- Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Product Series: LS  
Type: Incandescent  
Number Of Poles: 3-way

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No

CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121502  
UR: No

#### **DIMENSIONS**

Depth (US): 1.28"  
Height (US): 4.19"  
Width (US): 1.74"

#### **TECHNICAL INFORMATION**

Volts: 120V  
Watts: 600

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA  
Buy American Act Status: No