



TOGGLE SLIDE DIMMER MAGNETIC LOW VOLTAGE, SINGLE POLE / 3-WAY 700VA, RED

TSDLV703PRED | [Pass & Seymour](#)

FEATURES & BENEFITS

Replace your standard switch with the new Toggle Slide Dimmer by Legrand. The new Toggle Slide Dimmer offering has been optimized for today's complicated dimmable bulb market. Different bulbs require different dimming solutions and Legrand has you covered for all your lighting needs. The ergonomic slider was designed with the end user in mind making it easier to adjust in the dark or on the run.



- New aesthetically pleasing ergonomic design allows for easier operation.
- Convenient operation—combines ON/OFF toggle switch with separate slider for dimming control.
- All models are capable of single pole and 3-way operation.
- Rating: 700VA Magnetic Low Voltage; 120VAC, 60Hz.
- Constant memory returns lights to previous levels after a power failure.
- Screw-pressure-plate backwire terminals save time, space and money.
- Seven additional face cover colors available but sold separately (see TSDKIT*).
- Lifetime Warranty

SPECIFICATIONS

GENERAL INFO

Secure Environment: Indoor Use Only
Color: Red
Type: Magnetic Low Voltage Toggle
Number Of Poles: Single Pole / 3-Way
Number Of Wires: None
Style: Toggle

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listed: Yes
cULus: Yes
UL Standard: UL1472

DIMENSIONS

Depth (US): 1.40"
Height (US): 4.19" (2.68")
Length (US): 4.19"
Width (US): 1.73"
Product Weight (US): 3.51 oz.

TECHNICAL INFORMATION

Material: Polycarbonate
Volts: 120V
Volts (AC): 120 VAC
Watts: 700VA Magnetic Low Voltage
Grade Type: Spec Grade

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No