



TOGGLE SLIDE FAN SPEED CONTROL, SINGLE POLE / 3-WAY 1.6A, BLACK

TSDDH163PBK | [Pass & Seymour](#)

FEATURES & BENEFITS

Replace your standard switch with the new Toggle Slide Fan Control by Legrand. The new Toggle Slide Dimmer offering has been optimized for today's complicated dimmable bulb market. Different bulbs require different dimming solutions and Legrand has you covered for all your lighting needs. The ergonomic slider was designed with the end user in mind making it easier to adjust in the dark or on the run.

- New aesthetically pleasing ergonomic design allows for easier operation.
- Convenient operation—combines ON/OFF toggle switch with separate slider for fan speed control.
- All models are capable of single pole and 3-way operation.
- Rating: 1.6A, 120VAC, 60Hz
- Patented De-hummer technology virtually eliminates fan motor "hum".
- Constant memory returns the fan to previous levels after a power failure.
- Screw-pressure-plate backwire terminals save time, space and money.
- Seven additional face cover colors available but sold separately (see TSDKIT*).
- Lifetime Warranty

SPECIFICATIONS

GENERAL INFO

Secure Environment: Indoor Use Only

Color: Black

Type: Toggle

Number Of Poles: Single Pole / 3-Way

Number Of Wires: 4 Wires

Special Features: De-Hummer

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listed: Yes

cULus: Yes

UL Standard: UL1472

DIMENSIONS

Depth (US): 1.30"

Height (US): 4.25"
Length (US): 4.25"
Width (US): 1.73"
Product Weight (US): 3.24 oz.

TECHNICAL INFORMATION

Material: Polycarbonate
Volts: 120V
Volts (AC): 120 VAC
Watts: 1.6A
Grade Type: Spec Grade

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No