
HEAVY-DUTY, SHORT LENGTH, ROTATING EYE, K-TYPE

PS3001 | [Pass & Seymour](#)



FEATURES & BENEFITS

Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 3.00-3.490", Mesh Length - 30", Eye Diameter - 1 7/8", Break Strength - 48,000 lbs.



- K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.
- They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

SPECIFICATIONS

GENERAL INFO

Size: Short Length
Product Series: Flexcor
Type: K type
Duty: Heavy Duty
Special Features: Rotating Eye

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CSA Standard: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121722

UR: No

DIMENSIONS

Weight: 4.77977

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

