

---

## MEDIUM DUTY, STANDARD LENGTH, FLEXIBLE EYE, T-TYPE

PM1502 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 1.500-1.990", Mesh Length - 36", Eye Diameter - 7/16", Break Strength - 16,400 lbs.



- Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.
- Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

---

### SPECIFICATIONS

#### GENERAL INFO

Size: Standard Length  
Product Series: Flexcor  
Type: T-type  
Duty: Medium Duty

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121722  
UR: No

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

