
MULTI-WEAVE, FLEXIBLE EYE

P3002 | [Pass & Seymour](#)



FEATURES & BENEFITS

Multi-Weave, Flexible Eye. Cable Diameter - 3.000-3.490", Mesh Length - 54", Eye Diameter - 5/8", Break Strength - 48,000 lbs.

- Multi-weave pulling grips are constructed of high strength galvanized steel and are designed for pulling aluminum or copper bare conductor, wire rope and insulated cables.
- These grips are used in applications such as distribution line stringing and overhead transmission.
- Multi-weave pulling grips are available with a flexible and rotating eye, which can be attached to a swivel.
- Description — Rotating Eye: The forged steel rotating eye will thread through sheaves and blocks without binding, but is not a swivel and will not turn under tension.
- The rotating eye can turn to relieve pulling torque when tension is relaxed.

SPECIFICATIONS

GENERAL INFO

Product Series: Flexcor
Type: Multi-weave
Duty: Heavy Duty
Special Features: Flexible Eye

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121722
UR: No

DIMENSIONS

Weight: 0.79976

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

