



## MULTI-WEAVE, ROTATING EYE, LIGHT BLUE

P0751 | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Multi-Weave, Rotating Eye. Cable Diameter - 0.750-0.990", Mesh Length - 41", Eye Diameter - 1", Break Strength - 14,400 lbs. Light Blue.

- Multi-weave pulling grips are constructed of high strength galvanized steel and are designed for pulling aluminum or copper bare conductor, wire rope and insulated cables.
- These grips are used in applications such as distribution line stringing and overhead transmission.
- Multi-weave pulling grips are available with a flexible and rotating eye, which can be attached to a swivel.
- Description — Rotating Eye: The forged steel rotating eye will thread through sheaves and blocks without binding, but is not a swivel and will not turn under tension.
- The rotating eye can turn to relieve pulling torque when tension is relaxed.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Blue  
Product Series: Flexcor  
Type: Multi-weave  
Duty: Heavy Duty  
Special Features: Rotating Eye

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121722  
UR: No

#### DIMENSIONS

Weight: 0.47045

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

