
STRAIN RELIEF LIQUID-TIGHT GRIPS

STB45100SF | [Pass & Seymour](#)



FEATURES & BENEFITS

45 deg male liquid tight for metallic flexible conduit. 1" NPT, 5.25" Mesh length.

- Liquid-Tight grips are woven of stainless steel mesh with zinc plated steel or malleable iron bodies and nuts for corrosion resistance.
- They are used to connect liquid-tight flexible conduit to electrical enclosures to prevent conduit pullout.
- Each fitting is supplied with an insulated throat to provide conductor insulation and protect against damage by flexing, heat expansion and contraction.
- Liquid-Tight grips are recommended in the wiring of motors and any electrical enclosure where liquid-tight conduit is subject to motion or strain.

SPECIFICATIONS

GENERAL INFO

Typical Applications: Metallic Flexible Conduit

Product Series: Flexcor

Type: Strain Relief Liquid Tight Grips

Special Features: Straight Male

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: Yes

UN SPSC: 39121722

UR: No

DIMENSIONS

Weight: 0.52062

TECHNICAL INFORMATION

NPT Size: 1"

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

