
STRAIN RELIEF LIQUID-TIGHT GRIPS

STBN150SF | [Pass & Seymour](#)



FEATURES & BENEFITS

Straight male, liquid tight grips for non-metallic type A flexible Conduit. 1 1/2" NPT, 21.5" mesh length.

- Liquid-Tight grips are woven of stainless steel mesh with zinc plated steel or malleable iron bodies and nuts for corrosion resistance.
- They are used to connect liquid-tight flexible conduit to electrical enclosures to prevent conduit pullout.
- Each fitting is supplied with an insulated throat to provide conductor insulation and protect against damage by flexing, heat expansion and contraction.
- Liquid-Tight grips are recommended in the wiring of motors and any electrical enclosure where liquid-tight conduit is subject to motion or strain.

SPECIFICATIONS

GENERAL INFO

Typical Applications: Non-Metallic Type "A" Flexible Conduit

Product Series: Flexcor

Type: Strain Relief Liquid Tight Grips

Special Features: Straight Male

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121722

UR: No

TECHNICAL INFORMATION

NPT Size: 1-1/2"

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

