



STAINLESS STEEL CORD GRIP, 1 1/2" STRAIGHT, 1.0-1.12 OD RANGE

CGSS1501125 | [Pass & Seymour](#)

FEATURES & BENEFITS

The Pass & Seymour series of corrosion-resistant cord connectors feature a body and compression nut made of Type 304 stainless steel with exceptional tensile strength and the highest levels of durability in severely corrosive environments. All stainless steel cord grips include an embedded Buna-N O-Ring. These connectors are recommended for use in washdowns or high moisture environments in food processing plants, petrochemical facilities, wastewater treatment plants, pulp & paper mills and chemical manufacturing factories.

(Note: Type 316 stainless steel also available upon request and minimums may apply.)



- 304 grade Stainless Steel construction provides exceptional tensile strength and resists corrosion and impacts
- Includes an embedded Buna-N O-Ring providing a long term seal and protection against ingress
- The combination tightening surface provides a large wrenching area for easy installation
- Available in straight male from 3/8" to 3" NPT
- Also available in 316 grade stainless steel, upon request. Minimums may apply

SPECIFICATIONS

GENERAL INFO

Product Series: Flexcor

Type: Stainless Steel Cord Grips

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listed: Yes

UL Standard: Yes

TECHNICAL INFORMATION

Material: Stainless Steel

NEMA Rating: 3R

Rating (A): Stainless Steel 304 IP 67 68 Cord Grip

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

