

---

## STAINLESS STEEL STRAIN RELIEF CORD GRIP, 3/8" STRAIGHT, .25-.31 OD RANGE

CGSS38312M | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Stainless Steel Strain Relief Cord Grips are woven of stainless steel mesh with a Type 304 stainless steel body for corrosion resistance. They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain. They are recommended for indoor or outdoor use where subjected to moisture and corrosion in the wiring of pendant stations, processing equipment, hand tools, and power cord sets.



- 304 grade Stainless Steel body and mesh construction provides exceptional tensile strength and resists corrosion and impacts
- Includes an embedded Buna-N O-Ring providing a long-term seal and protection against ingress
- The combination tightening surface provides a large wrenching area for easy installation
- Available in straight male fittings from 1/2" to 3" NPT
- Also available in 316 grade stainless steel, upon request. Minimums may apply

---

### SPECIFICATIONS

#### GENERAL INFO

Product Series: Flexcor  
Type: Stainless Steel Strain Relief Cord Grips

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listed: Yes  
UL Standard: Yes

#### TECHNICAL INFORMATION

Material: Stainless Steel  
NEMA Rating: 3R

Rating (A): Stainless Steel 304 IP 67 68 Cord Grip

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA

