
STAINLESS STEEL SUPPORT GRIPS STANDARD DUTY, CLOSED MESH

FC3000FSS | [Pass & Seymour](#)



FEATURES & BENEFITS

Stainless Steel, Standard-duty, Closed mesh, Offset eye grips. Cable diameter 3.000-3.490", Bale length - 9", Mesh length - 26", Break strength - 5,040 lbs.

- Standard closed mesh support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Closed mesh support grips are used when the end of the cable is accessible.
- Support grips are woven of corrosion-resistant stainless steel wire.
- Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

SPECIFICATIONS

GENERAL INFO

Typical Applications: Service Drop
Product Series: Flexcor
Type: Closed Mesh
Duty: Standard Duty
Special Features: Offset Eye

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: No
UN SPSC: 39121722
UR: No

DIMENSIONS

Weight: 0.9503

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

