

---

## SUPPORT GRIPS STANDARD DUTY, SPLIT LACE

FS125UU | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Standard duty, Split lace, Double eye. Cable diameter- 1.250-1.4990", Bale length - 5", Mesh length - 16", Break strength - 1,920 lbs.



- Split lace support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation.
- Support grips are woven of corrosion-resistant tinned-bronze wire.
- Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

---

### SPECIFICATIONS

#### GENERAL INFO

Typical Applications: Service Drop  
Product Series: Flexcor  
Type: Split Lace  
Duty: Standard Duty  
Special Features: Double Eye

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No

Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121722  
UR: No

**DIMENSIONS**

Weight: 0.38106

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

