
STAINLESS STEEL SUPPORT GRIPS STANDARD DUTY, SPLIT LACE

FS1000FSS | [Pass & Seymour](#)



FEATURES & BENEFITS

Stainless Steel, Standard-duty, Split lace, Offset eye. Cable diameter - 1.000-1.240", Bale length 5", Mesh length 15", Break strength - 1,680 lbs.

- Split lace support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation.
- Support grips are woven of corrosion-resistant stainless steel wire.
- Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

SPECIFICATIONS

GENERAL INFO

Typical Applications: Service Drop

Product Series: Flexcor

Type: Split Lace

Duty: Standard Duty

Special Features: Offset Eye

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121722

UR: No

DIMENSIONS

Weight: 0.2785

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

