
SUPPORT GRIPS STANDARD DUTY, SPLIT ROD

FR175UU | [Pass & Seymour](#)



FEATURES & BENEFITS

Standard duty, Split rod, Double eye. Cable diameter - 1.750-1.990", Bale length - 6", Mesh length - 20", Break strength - 2,640 lbs.



- Split rod support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Split rod support grips are used when the end of the cable cannot be easily accessed and the installation is temporary.
- Support grips are woven of corrosion-resistant tinned-bronze wire.
- Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

SPECIFICATIONS

GENERAL INFO

Typical Applications: Service Drop

Product Series: Flexcor

Type: Split Rod

Duty: Standard Duty

Special Features: Double Eye

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No
UL Listing No: No
UN SPSC: 39121722
UR: No

DIMENSIONS

Weight: 1.45525

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

