

---

## STAINLESS STEEL SUPPORT GRIPS STANDARD DUTY, SPLIT ROD

FR125LBSS | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Stainless Steel, Standard-duty, Split rod, Locking bale (universal eye). Cable diameter - 1.250-1.490", Bale length - 14", Mesh length - 15", Break strength - 1,920 lbs.

- Split rod support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Split rod support grips are used when the end of the cable cannot be easily accessed and the installation is temporary.
- Support grips are woven of corrosion-resistant stainless steel wire.
- Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

---

### SPECIFICATIONS

#### GENERAL INFO

Typical Applications: Service Drop  
Product Series: Flexcor  
Type: Split Rod  
Duty: Standard Duty  
Special Features: Locking Bale

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121722  
UR: No

#### DIMENSIONS

Weight: 0.49397

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

