
SUPPORT GRIPS STANDARD DUTY, SPLIT ROD

FR2000F | [Pass & Seymour](#)



FEATURES & BENEFITS

Standard-duty, Split rod, Offset eye. Cable diameter - 2.000-2.490", Bale length - 6", Mesh length - 22", Break strength - 3,760 lbs.

- Split rod support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Split rod support grips are used when the end of the cable cannot be easily accessed and the installation is temporary.
- Support grips are woven of corrosion-resistant tinned-bronze wire.
- Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

SPECIFICATIONS

GENERAL INFO

Typical Applications: Service Drop
Product Series: Flexcor
Type: Split Rod
Duty: Standard Duty
Special Features: Offset Eye

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: No
UN SPSC: 39121722
UR: No

DIMENSIONS

Weight: 0.85621

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

