



PLUGTAIL® HOSPITAL GRADE TAMPER-RESISTANT WEATHER-RESISTANT SELF-TEST GFCI, GRAY

PT2097HGTRWRGRY | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail® Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCI receptacles with SafeLock® Protection conduct an automatic test every three seconds, ensuring they're always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

For detailed GFCI receptacle information, visit our [GFCI Headquarters](#).



- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing three-wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings.
- Large crimped and welded brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL-Listed, finger-safe housing.
- Patented SafeLock® Protection -- if critical components are damaged and ground-fault protection is lost, power to the receptacle is disconnected.
- The indicator light flashes if the device fails the self-test, signalling that the GFCI should be replaced.
- Tamper-resistant automatic shutter system prevents young children from inserting common household objects.
- Captive zinc-plated steel mounting screws make for easier installation.
- The most durable GFCI available: Exceeds UL943 voltage surge requirements.
- Auto-ground clip assures a positive ground to metal box.
- UV-resistant nylon construction for superior strength and durability.

SPECIFICATIONS

GENERAL INFO

Color: Gray

UL Standards Tested: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: CSA C22.2 No. 42, CSA C22.2 No. 144

CSA Listed: Yes

CSA Standard: CSA C22.2 No. 42

cULus: Yes

Federal Spec: Yes

UL Standard: UL498, UL943

DIMENSIONS

Depth (US): 1.2"

Height (US): 4.20"

Width (US): 1.73"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

Volts: 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: Trade Agreement Act Compliant