



PLUGTAIL® SPEC-GRADE 20A SELF-TEST DUPLEX GFCI, LIGHT ALMOND

PT2097LA | [Pass & Seymour](#)

FEATURES & BENEFITS

The fastest-installing GFCI ever now conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock™ Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

For detailed GFCI receptacle information, visit our [GFCI Headquarters](#).



- Faster, more reliable installation.
- No exposed terminals create a finger-safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail® Connector.
- GFCI works with existing 3-wire PlugTail Connectors creating a non-feed-thru application for facility owners.
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.
- Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box.
- Auto-Ground clip assures a positive ground to metal box.
- Meets 2015 UL requirements.
- Exceeds UL 943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- 10kA short circuit rating.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.

- Class A rated GFCI.
 - Supplied with matching TP wall plate.
 - Tri-drive screws.
 - Supply Voltage: 125VAC, 60 Hz
 - Supply Voltage Range: 102-132 VAC
 - Trip Threshold: 5 +/- 1 mA
 - Trip Time: 0.025 sec., nominal per UL Standard
-

SPECIFICATIONS

GENERAL INFO

Color: Light Almond

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 111

CSA Listed: No

CSA Standard: Yes

cULus: Yes

Federal Spec: Yes

UL Standard: UL498

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

Volts: 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: Buy American Act Compliant