
100A 4 POLE 5 WIRE FUSIBLE MECHANICAL INTERLOCK

PS5100FMIR5W | [Pass & Seymour](#)



FEATURES & BENEFITS

Four pole, Five wire, Fusible Mechanical Interlock Receptacle. 100 amp, 3ØY, 347/600 vac.

- Top or Bottom feed.
- Unit shipped with no holes drilled; a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

SPECIFICATIONS

GENERAL INFO

Type: Pin & Sleeve Fusible Mechanical Interlock

Number Of Poles: 4

Number Of Wires: 5

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes

UL Listing No: No

UN SPSC: 39121403

UR: No

DIMENSIONS

Depth (US): 29.7

Width (US): 12.5

Volume: 3564

Weight: 17.48

Height: 9.6

TECHNICAL INFORMATION

Amps: 100A

Volts: 3ØY 347/600VAC

Volts (AC): 347/600

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

