



30A 4 POLE 5 WIRE FUSIBLE MECHANICAL INTERLOCK

PS530FMIR9W | [Pass & Seymour](#)

FEATURES & BENEFITS

Four pole, Five wire, Fusible Mechanical Interlock Receptacle. 3Ø amp, 208 volt.

- Top or Bottom feed.
- Unit shipped with no holes drilled; a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

SPECIFICATIONS

GENERAL INFO

Type: Pin & Sleeve Fusible Mechanical Interlock

Number Of Poles: 4

Number Of Wires: 5

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes

UL Listing No: No

UN SPSC: 39121403

DIMENSIONS

Depth (US): 25

Width (US): 7.62

Volume: 2047.875

Weight: 10.44

Height: 10.75

TECHNICAL INFORMATION

Amps: 30A

Volts: 3ØY 120/208VAC

Volts (AC): 120/280

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

