



## NON-FUSIBLE MECHANICAL INTERLOCK

PS420MIR9W | [Pass & Seymour](#)

### FEATURES & BENEFITS

Three pole, Four wire, Non-Fusible Mechanical Interlock Receptacle. 20 amp, 3Ø, 240 vac.



- Top or Bottom feed.
- Unit shipped with no holes drilled; a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

### SPECIFICATIONS

#### GENERAL INFO

Type: Pin & Sleeve North American Watertight Non-Fusible Mechanical Interlock

Number Of Poles: 3

Number Of Wires: 4

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

UL Listing No: E31169

UL Standard: Yes

UN SPSC: 39121403

#### TECHNICAL INFORMATION

Amps: 20A

Volts: 3Ø 240VAC

Volts (AC): 250

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

