



NON-FUSIBLE MECHANICAL INTERLOCK

PS430MIR5W | [Pass & Seymour](#)

FEATURES & BENEFITS

Triple pole, Four wire, Non-Fusible Mechanical Interlock Receptacle. 30 amp, 3Ø, 600 vac.



- Top or Bottom feed.
- Unit shipped with no holes drilled; a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

SPECIFICATIONS

GENERAL INFO

Type: Pin & Sleeve North American Watertight Non-Fusible Mechanical Interlock

Number Of Poles: 3

Number Of Wires: 4

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

UL Listing No: E311169

UL Standard: Yes

UN SPSC: 39121403

TECHNICAL INFORMATION

Amps: 30A

Volts: 3Ø 600VAC

Volts (AC): 600

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

