



## 63A PIN & SLEEVE INTERNATIONAL SPLASHPROOF RECEPTACLE

PS463R9S | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Splashproof Receptacle, 3 Pole 4 Wire, 63Amp IP44 Suitability. 200/250 volt.

- All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.
- North American products come completely ready to wire, for quick, simple installation. And all feature chemical-resistant thermoplastic construction.
- Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.
- An exclusive, hinged cord grip eliminates loose parts that get lost.

---

### SPECIFICATIONS

#### GENERAL INFO

Type: Pin & Sleeve Splashproof Surface Receptacle

Number Of Poles: 3

Number Of Wires: 4

#### TECHNICAL INFORMATION

Amps: 63A

Volts: 200/250

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: FRANCE

Buy American Act Status: Trade Agreement Act Compliant