

---

## 32A PIN & SLEEVE INTERNATIONAL WATERTIGHT RECEPTACLE



PS332R6W | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Double pole, Three wire, Pin and Sleeve Watertight Receptacle. 32 amp, 200/250 volt.

- All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.
- Products come completely ready to wire, for quick, simple installation.
- And all feature chemical-resistant thermoplastic construction.
- Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.
- An exclusive, hinged cord grip eliminates loose parts that get lost.

---

### SPECIFICATIONS

#### GENERAL INFO

Type: Pin & Sleeve International Watertight Receptacle

Number Of Poles: 2

Number Of Wires: 3

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UR: No

#### DIMENSIONS

Length (US): 6.6"

#### TECHNICAL INFORMATION

Amps: 32A

Volts: 200/250

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

