
60A PIN & SLEEVE INLET

PS460B7W | [Pass & Seymour](#)



FEATURES & BENEFITS

Three pole, Four wire, Pin and Sleeve Inlet. 60 amp, 3Ø/480 volt.



- All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.
- North American products come completely ready to wire, for quick, simple installation.
- And all feature chemical-resistant thermoplastic construction.
- Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.
- An exclusive, hinged cord grip eliminates loose parts that get lost.

SPECIFICATIONS

GENERAL INFO

Type: Pin & Sleeve North American Watertight Inlet

Number Of Poles: 3

Number Of Wires: 4

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121403

UR: No

DIMENSIONS

Length (US): 4.25"

Width (US): 4.5"

TECHNICAL INFORMATION

Amps: 60A

Volts: 3ø 480VAC

Volts (AC): 480

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

