
60A PIN & SLEEVE PLUG

PS560P7W | [Pass & Seymour](#)



FEATURES & BENEFITS

Four pole, Five wire, Pin and Sleeve Plug. 6Ø amp, 277/480 vac.



- All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.
- North American products come completely ready to wire, for quick, simple installation.
- And all feature chemical-resistant thermoplastic construction.
- Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.
- An exclusive, hinged cord grip eliminates loose parts that get lost.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Type: Pin & Sleeve North American Watertight Plug

Number Of Poles: 4

Number Of Wires: 5

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CSA Standard: Yes

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No
UN SPSC: 39121403
UR: No

DIMENSIONS

Length (US): 10"

TECHNICAL INFORMATION

Amps: 60A
Volts: 3ØY 277/480VAC
Volts (AC): 277/480

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

