

---

## MOGUL BASE LAMPHOLDER

8678 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Mogul base, porcelain, keyless, single circuit, 1/4" IPS 13/16" hexagon x 9/16" high with screw set. White.



- Quality Materials.
- Durability.
- Time-tested design.

---

### SPECIFICATIONS

#### GENERAL INFO

Type: Incandescent Mogul Base Lampholder

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39111803  
UR: No

#### DIMENSIONS

Diameter (US): 3.12"  
Height: 3.25"

#### TECHNICAL INFORMATION

Volts: 600V  
Volts (AC): 600  
Watts: 1500

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

