



## 15A, 120V TRADEMASTER® 3-WAY/ILLUMINATED TOGGLE SWITCH, IVORY

663ISLG | [Pass & Seymour](#)

### FEATURES & BENEFITS

Three-way Lighted Toggle Switch. 15 amps, 120 volts, Ivory.



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- This switch is compatible with incandescent loads only and is not recommended for use with LED or CFL lamps.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Product Series: TradeMaster  
Type: Toggle  
Number Of Poles: 3-way  
Special Features: Self-Grounding

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 111  
CSA Standard: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121406

## DIMENSIONS

Depth (US): 1.090"

Height (US): 3.281"

Width (US): 1.25"

## TECHNICAL INFORMATION

Amps: 15A

Volts: 120

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

