



TITAN SERIES FLUORESCENT 2 WIRE DIMMER, GRAY

CDFB5GRY | [Pass & Seymour](#)

FEATURES & BENEFITS

Slide Dimmer, Electronic Single Pole 2Wire 5A, Gray



- For use with 2 wire 120V and 277V fluorescent dimming ballasts.
- Field configurable wall plate system.
- Labeling system.
- Adjustable low end output voltage.
- Shipped with protective film.
- Rugged construction.
- Superior ratings with a minimum of derating when ganged.
- Simple to plan the rough-in.
- Available in single pole slide-to-OFF and single pole/3-way preset models.
- Attractive European styling.
- Eye-catching packaging.
- Exclusive adaptor kit to install other Decorator opening devices under the Titan™ wall plate system.
- Blank center plate included.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Gray
Size: Narrow
Product Series: Titan
Type: Fluorescent
Number Of Poles: 1
Number Of Wires: 2
Style: Narrow

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPSC: 39121559
UR: No

DIMENSIONS

Depth (US): 1.44"
Height (US): 4.87"
Width (US): 2.85"

TECHNICAL INFORMATION

Amps: 5A
Volts: 120V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No