



## TITAN SERIES FLUORESCENT 3 WIRE DIMMER, IVORY

CD3FB103P277I | [Pass & Seymour](#)

### FEATURES & BENEFITS

Slide Dimmer, Electronic Single Pole/3Way 3Wire PRESET 10A277V, Ivory



- For use with 3 wire 120V and 277V fluorescent dimming ballasts.
- Field configurable wall plate system.
- Labeling system.
- Adjustable low end output voltage.
- Shipped with protective film.
- Rugged construction.
- Superior ratings with a minimum of derating when ganged.
- Simple to plan the rough-in.
- Available in single pole slide-to-OFF and single pole/3-way preset models.
- Attractive European styling. Eye-catching packaging.
- Exclusive adaptor kit to install other Decorator opening devices under the Titan™ wall plate system. (See Page N-29.)
- Blank center plate included.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Size: Narrow  
Product Series: Titan  
Type: Fluorescent  
Number Of Poles: 1  
Number Of Wires: 3  
Style: Narrow

## LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121559  
UR: No

## DIMENSIONS

Depth (US): 1.44"  
Height (US): 4.87"  
Width (US): 2.85"

## TECHNICAL INFORMATION

Amps: 10A  
Volts: 277V

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA  
Buy American Act Status: No