



TITAN® SERIES LED 4-WIRE SINGLE-POLE/3-WAY PRESET DIMMER, WHITE

CD4FBL3PW | [Pass & Seymour](#)

FEATURES & BENEFITS

P&S Titan Dimmers offer a complete solution for easy, economical multi-gang dimmer installation in commercial jobs. Designed to handle 0-10V dimming in Fluorescent and LED fixtures.



- Includes integrated power pack and blank center plate.
- Field configurable wall plate system.
- Labeling system.
- Adjustable low end trim.
- Shipped with protective film.
- Rugged construction.
- Superior ratings with a minimum of derating when ganged.
- Simple to plan the rough-in.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Size: Narrow
Product Series: Titan
Type: LED
Number Of Poles: 3-Way
Number Of Wires: 4
Style: Narrow

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listed: No

cULus: Yes

DIMENSIONS

Depth (US): 1.4375"

Height (US): 4.87"

Width (US): 2.85"

TECHNICAL INFORMATION

Rating (A): 120 VAC 10A/ 277 VAC 5A

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA