
TITAN SERIES MAGNETIC LOW-VOLTAGE DIMMER, WHITE

CDLV1603PW | [Pass & Seymour](#)



FEATURES & BENEFITS

Slide Dimmer, Low Voltage, Single Pole/3Way PRESET 1600VA, White



- Field configurable wall plate system.
- Labeling system.
- Adjustable low end output voltage.
- Shipped with protective film.
- Rugged construction.
- Superior ratings with a minimum of de-rating when ganged.
- Simple to plan the rough-in.
- Available in single pole slide-to-OFF and single pole/3-way preset models.
- Attractive European styling.
- Eye-catching packaging.
- Exclusive adaptor kit to install other Decorator opening devices under the Titan™ wall plate system.
- Blank center plate included.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Size: Wide
Product Series: Titan
Type: Magnetic Low Voltage
Number Of Poles: 3-Way
Style: Wide

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121559
UR: No

TECHNICAL INFORMATION

Volts: 120V
Watts: 1600

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No