

---

## TITAN SERIES FAN SPEED CONTROL, BLACK

CDSC12BK | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

#### SLIDE CONTROL 12A VARIABLE, BLACK



- Field configurable wall plate system.
- Labeling system.
- Shipped with protective film.
- Rugged construction.
- Simple to plan the rough-in.
- Available in single pole slide-to-OFF models.
- Attractive European styling.
- Eye-catching packaging.
- Exclusive adaptor kit to install other Decorator opening devices under the Titan™ wall plate system. (See Page N-29.)
- Available in both continuously variable and de-hummer styles.
- Blank center plate included.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Size: Wide  
Product Series: Titan  
Type: Wide  
Style: Wide

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No

CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121559  
UR: No

#### **TECHNICAL INFORMATION**

Amps: 12A  
Volts: 120V

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA  
Buy American Act Status: No