



## COMMERCIAL OCCUPANCY DÉTECTEUR, WHITE

CS1200 | [Pass & Seymour](#)

### FEATURES & BENEFITS

PIR Ceiling Sensor, 24VDC Input, Coverage 360degree, 1200 Sq.Ft.



- ASIC technology reduces components and enhances reliability.
- Pulse count processing eliminates false offs without reducing sensitivity.
- Detection signature analysis eliminates false triggers and proves immunity to RFI and EMI.
- Low-profile design ensures a clean and uncluttered ceiling appearance.
- User-adjustable time delay from 15 seconds to 30 minutes by two minute increments.
- Sensitivity is programmed through a DIP switch and has four settings from minimum to maximum.
- Dual-element, temperature compensated pyro-electric sensor.
- Mounting options: ceiling tile or 3.0 inch round mudring.
- Units per power pack: up to 13.
- cULus listed.
- 5-year warranty.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: Occupancy

Features: Passive Infrared

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

UN SPSC: 39121559

## DIMENSIONS

Depth (US): 2.20"

Diameter (US): 3.30"

## TECHNICAL INFORMATION

Amps: 11mA

Mounting: Ceiling

Volts: 24VDC

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No