

---

## POWER OUTLET RECEPTACLE OPENINGS, TWO GANG, ALUMINUM

SA716 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Two Gang Power Outlet Receptacle Opening, 2.2813" hole for 2.125" diameter device - 4 mtg. holes, Smooth Metal.

- Aluminum: .040" thick.
- Lustrous satin finish.
- Lacquered to prevent corrosion.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

---

### SPECIFICATIONS

#### GENERAL INFO

Discontinued: Yes  
Size: Standard  
Type: Single

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121704  
UR: No

#### DIMENSIONS

Diameter (US): 2.2813" Hole

## TECHNICAL INFORMATION

Material: Aluminum

Capacity: 2-gang

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

